

Flow Rates in LPM (GPM) per Channel

Speed (rpm)	Precision pump tubing			High-performance precision pump tubing		
	I/P® 26	I/P 73	I/P 82	I/P 70	I/P 88	I/P 89
33 to 650	0.20 to 4.0 (0.05 to 1.0)	0.41 to 8.0 (0.11 to 2.1)	0.66 to 13.0 (0.18 to 3.5)	0.41 to 8.0 (0.11 to 2.1)	0.66 to 17.0 (0.18 to 4.5)	0.86 to 19.0 (0.23 to 5.0)

Specifications & Ordering Information for Variable-Speed Brushless Drives

ISO 9001:2000 SUPPLIER CERTIFIED    2 year warranty

Catalog number	Motor size	Motor speed (rpm)	Speed control (repeatability)	Pump heads accepted	IP rating	Dimensions (L x W x H)	Power (50/60 Hz)		Price
							VAC	Amps	
Variable-speed brushless process drive									
R-77410-10	1/8 hp (0.25 kW)	33 to 650	±0.25% (2% of max rpm)	2	IP55	14" x 10" x 9 1/8" (34.2 x 25.2 x 23 cm)	90 to 260	4.5 A at 115 VAC 2.6 A at 230 VAC	
Variable-speed brushless process drive with remote I/O									
R-77411-00	1/8 hp (0.25 kW)	33 to 650	±0.25% (2% of max rpm)	2	IP55	14" x 10" x 9 1/8" (34.2 x 25.2 x 23 cm)	90 to 260	2.6 A at 230 VAC 4.5 A at 115 VAC	

Accessories (for 77411-00 only)

R-07595-43 Washdown foot switch R-77300-32 Remote cable kit

Complete I/P® Brushless Process Pump Systems

Complete Systems 1 and 2 include:

Pump Head	+	Tubing	+	Drive
1 I/P® Easy-Load® pump head 77601-10 (page 1508)		Tygon® LFL I/P 73 tubing 06429-73 10 ft (3 m) (page 1511)		I/P Brushless process drive 77410-10 33 to 650 rpm (above)
2 I/P High-Performance pump head 77600-62 (page 1509)		Tygon LFL I/P 88 tubing 06429-88 3 ft (1 m) (page 1511)		I/P Brushless process drive 77410-10 33 to 650 rpm (above)

Catalog number	Description	Power	Price
1 R-77963-10	I/P brushless process system with Easy-Load pump head	90 to 260 VAC, 50/60 Hz	
2 R-77963-20	I/P brushless process system with High-Performance pump head		

Note: Order accessories separately above.

Flow Range:
0.41 to 8.0 LPM

1
77963-10



2
77963-20

Flow Range:
0.66 to 17.0 LPM

Complete Systems 3 and 4 include:

Pump Head	+	Tubing	+	Drive
3 I/P® Easy-Load® pump head 77601-10 (page 1508)		Tygon® LFL I/P 73 tubing 06429-73 10 ft (3 m) (page 1511)		I/P Brushless process drive 77411-00 33 to 650 rpm (above)
4 I/P High-Performance pump head 77600-62 (page 1509)		Tygon LFL I/P 88 tubing 06429-88 3 ft (1 m) (page 1511)		I/P Brushless process drive 77411-00 33 to 650 rpm (above)

Catalog number	Description	Power	Price
3 R-77965-00	I/P brushless process system with remote I/O and Easy-Load pump head	90 to 260 VAC, 50/60 Hz	
4 R-77965-10	I/P brushless process system with remote I/O and High-Performance pump head		

Note: Order accessories separately above.

Flow Range:
0.41 to 8.0 LPM

3
77965-00



4
77965-10

Flow Range:
0.66 to 17.0 LPM