



Platform Trucks with Removable Handles

Built to accommodate oversized items. Enameled steel deck and angle subframe make these trucks durable.

Trucks 47350-00 and -10 have 5" diameter, nonmarking polyurethane casters. High-capacity trucks 47350-20 and -30 have 6" molded-on rubber casters. Handle extends 28" above deck.

47350-00

Catalog number	Capacity lb (kg)	Deck size (L x W)	Caster diameter	Shpg wt lb (kg)	Price
A-47350-00	1000 (454)	32" x 18"	5"	39 (17.7)	
A-47350-10	1000 (454)	48" x 24"	5"	56 (25.4)	
A-47350-20	1600 (726)	36" x 24"	6"	71 (32.2)	
A-47350-30	1600 (726)	60" x 24"	6"	88 (40.0)	



Stainless Steel Platform Truck

This durable truck features a leak-proof bottom supported by a heavy angle iron frame—it holds up to 200 lb (91 kg). Includes chrome-plated tubular steel handle and 4" swivel casters. Platform is made of 430 SS; measures 20¾" L x 20¾" W x 6" H. Truck measures 27" L x 20⅞" W x 32" H overall.

09370-00

Catalog number	Capacity lb (kg)	Deck size (L x W)	Caster diameter	Shpg wt lb (kg)	Price
A-09370-00	200 (91)	20¾" x 20¾"	4"	28 (12.8)	

ColeParmer.com

Satisfying your Search...

For additional capacities and USDA-approved platform trucks, enter "Rubbermaid platform trucks" into the online "Catalog Search" box and click "Go."



47200-01



Platform Trucks

These plastic platform trucks are maintenance-free and virtually indestructible—won't rust, dent, or warp like metal or wood trucks. Sturdy handle secures your load and offers easy mobility. Trucks are ideal for moving large or bulky loads.

Specifications & Ordering Information

Catalog number	Capacity lb (kg)	Platform size	Caster size (dia x W)	Number of handles	Shpg wt lb (kg)	Price
A-47200-01	1000 (454)	36" x 24"	6" x 2" rubber	1	63 (28.6)	
A-47200-10	1000 (454)	48" x 24"	6" x 2" rubber	1	78 (35.4)	
A-47200-19	1000 (454)	60" x 30"	6" x 2" rubber	2	88 (40.0)	



86412-52



Dollies

Use these dollies to easily transport heavy and oversized loads and reduce the need for carrying and lifting. Both units feature wide, nonmarking casters for added stability and control and a sturdy structural-foam platform that won't chip, dent, rust, or peel. Nonskid platform surface keeps loads from shifting; plastic construction is easy on doors and walls. Each unit has 200 lb (90.7 kg) capacity.

Flat dolly is ideal for handling oversized loads. Dolly 86412-52 features a three-position handle which can be folded flat or used to push or pull loads.

Catalog number	Description	Dimensions (L x W x H)	Shpg wt lb (kg)	Price
A-86412-50	Flat dolly	23" x 18" x 7⅞"	10 (4.6)	
A-86412-52	Dolly with three-position handle	23" x 18" x 7⅞"	11 (5.0)	

Round Dolly

This rugged industrial grade dolly will not rust, chip, or peel. Heavy-duty swivel casters provide easy mobility. Measures 24⅜" dia x 7⅞" H—ideal for transport of waste containers or drums.

A-06738-40 Dolly.
Shpg wt 15 lb (6.9 kg)



Move heavy cylinders



Transport cylinders safely with this sturdy dolly. Strong polyethylene construction is rust and corrosion-resistant and easily handles heavy industrial cylinders. Heavy-duty nylon strap secures cylinders in place. Built-in tool pocket makes it easy to carry tools and gear. Dolly accommodates cylinders up to 10" in diameter and has a load bearing capacity of 200 lb (90 kg). Dolly measures 18" L x 30" W x 42¼" H.

BH-86109-60 Cylinder dolly

You'll find more equipment for cylinder storage on page 1658.