

Autoclave Gloves

Heat resistant to 450°F (232°C)



Use these soft, pliant, and all-cotton terry cloth gloves to handle hot objects fresh from the autoclave or oven. Excellent for use in any environment where heat protection is required. Two lengths provide optimum protection to your wrists and forearms. Bright orange for increased visibility. Machine wash, tumble dry.

Approval: CE

| Catalog number | Length | Price per pair | |
|----------------------------|--------|----------------|-------|
| | | 1 pr | 12 pr |
| A-06496-40 | 13" | | |
| A-06496-42 | 18½" | | |

JOMAC® Polarflex® and Polarflex 2® Cold-Weather Gloves

Lined PVC gloves provide maximum protection against liquids in cold and freezing weather

Polarflex Gloves feature nylon foam insulation and a fully coated knit wrist for extra protection against the cold. Nylon foam lining can be removed and laundered to extend the life of the glove.

Polarflex 2 Gloves are designed for jobs requiring added flexibility and better grip. They are fully insulated and feature a gauntlet cuff for added wrist protection. Nonslip, textured finish ensures a good grip.



| Catalog number | Glove description | Length | Price per pair | |
|----------------------------|-------------------|--------|----------------|-------|
| | | | 1 pr | 12 pr |
| A-86221-40 | Polarflex | 14" | | |
| A-86221-50 | Polarflex 2 | 12" | | |
| A-86221-52 | Polarflex 2 | 14" | | |

Rack'em™ Glove Rack



Economical rack helps gloves dry by holding them open and upright. Use rack to keep gloves in one place and prevent them from cracking and permanently bending. Rack holds four pairs of gloves in all styles and sizes. Made from galvanized steel.

[A-40486-06](#) Glove rack

MAPA PROFESSIONAL Temp-Tec® Heat-Insulated Neoprene Gloves

Two-tone wear indicator warns you when to replace gloves

These gloves are made of synthetic neoprene rubber for good chemical resistance. Easily maintain your grip with the nonslip, roughened surface. Withstand temperatures from -100 to 480°F (-73 to 249°C). The 14"L gloves feature integral cotton fleece liner; 26"L gloves feature removable washable cotton liner.

Approval: CE

Compliance: USDA accepted per 21CFR 177.2600



Insulated neoprene gloves give you excellent protection from extreme hot or cold.

| Catalog number | Size | Length | Thickness | Price per pair | |
|----------------------------|---------|--------|-------------|----------------|------|
| | | | | 1 pr | 6 pr |
| A-40211-30 | Medium | 14" | Heavy gauge | | |
| A-40211-31 | Large | | | | |
| A-40211-32 | X-large | | | | |
| A-40211-70 | Medium | 26" | Heavy gauge | | |
| A-40211-71 | Large | | | | |
| A-40211-72 | X-large | | | | |

ColeParmer.com Satisfying your Search™

- Quick, convenient online ordering
- Track Web and non-Web orders in real time



Ansell Protective Products Thermaprene™ Heat-Resistant, Lined Neoprene Gloves



Gloves are insulated to protect against intermittent contact with heated surfaces up to 400°F (204°C). Comfortable cotton knit lining provides extra protection against punctures. Nonslip grip.

Approval: CE

| Catalog number | Size | Length | Price per pair | |
|----------------------------|------|--------|----------------|------|
| | | | 1 pr | 6 pr |
| A-81609-00 | 8 | 18" | | |
| A-81609-02 | 10 | | | |
| A-81609-04 | 8 | 26" | | |
| A-81609-06 | 10 | | | |