

buy more,  
save more

6-29 packs save 10%    30-119 packs save 15%    120+ packs save 20%  
Mix and match packs of any items from the "blue" tables to save!

## Bottles Bo

Wide Mouth

### Cole-Parmer Wide-Mouth Bottles, PP

Cost-effective, rigid leakproof polypropylene (PP) bottles offer excellent chemical resistance and are ideal for storage and sampling of liquids or solids. Include PP closures. **Autoclavable.**

Catalog number	Capacity mL (oz)	Cap size	Qty/ cs	Price/ cs	Save 10% 6-29 cs	Save 15% 30-120 cs	Save 20% 120+
K-06045-41	30 (1)	28 mm	72				
K-06045-43	60 (2)	33 mm	72				
K-06045-45	125 (4)	38 mm	72				
K-06045-47	250 (8)	45 mm	72				
K-06045-49	500 (16)	55 mm	48				
K-06045-51	1000 (32)	65 mm	24				
K-06045-53	2000 (64)	65 mm	6				



### NALGENE® Wide-Mouth Bottles, PP

These bottles are suitable whenever autoclaving is required. All have leakproof polypropylene (PP) screw closures. **Autoclavable.**

Catalog number	Capacity mL (oz)	Cap size	Qty/ pk	Price/ 1 pk	Save 10% 6-29 pks	Save 15% 30-119 pks	Save 20% 120+ pks
K-06048-01	30 (1)	28 mm					
K-06048-02	60 (2)	28 mm					
K-06048-10	125 (4)	38 mm	12				
K-06048-20	250 (8)	43 mm					
K-06048-30	500 (16)	53 mm					
K-06048-40	1000 (32)	63 mm	6				
<b>Replacement caps, PP</b>							
K-63000-06	—	28 mm					
K-63000-10	—	43 mm					
K-63000-12	—	53 mm	12				
K-63000-14	—	63 mm					



### Graduated Bottles, PP

Manufactured in translucent polypropylene, these bottles are chemical resistant, leakproof, and allow safe storage for a wide variety of liquids and solids. Bottles are wide-mouth for easy filling, and have printed graduations in both milliliters and fluid ounces. Screw caps included. **Autoclavable.**

Catalog number	Capacity mL (oz)	Cap size	Qty/ pk	Price/ 1 pk	Save 10% 6-29 pks	Save 15% 30-119 pks	Save 20% 120+ pks
K-06041-10	60 (2)	33 mm	12				
K-06041-12	125 (4)	38 mm	12				
K-06041-14	250 (8)	45 mm	12				
K-06041-16	500 (16)	55 mm	12				
K-06041-18	1000 (32)	65 mm	6				



### NALGENE® Wide-Mouth Bottles, Teflon® FEP

The most inert bottles available are those made of Teflon® FEP. They will withstand repeated sterilization and temperatures from -157 to 302°F (-105 to 150°C). Use them for cryogenic experiments, trace metal analysis, and organic solvents. All have leakproof Tefzel® ETFE screw closures. **Autoclavable.**

Catalog number	Capacity (mL)	Cap size	Qty/ pk	Price/ 1 pk	Save 10% 6-29 pks	Save 15% 30-119 pks	Save 20% 120+ pks
<b>Bottles, Teflon FEP</b>							
K-06044-10	125 (4)	33 mm					
K-06044-20	250 (8)	43 mm					
K-06044-30	500 (16)	48 mm	1				
K-06044-40	1000 (32)	53 mm					
K-06044-42	2000 (64)	53 mm					
<b>Replacement caps, PP</b>							
K-63001-00	—	33 mm					
K-63001-02	—	43 mm					
K-63001-04	—	48 mm	2				
K-63001-06	—	53 mm					

