

**buy more,
save more**

10-49 packs **save 10%** 50-99 packs **save 15%** 100+ packs **save 20%**
 Mix and match packs of any items from the "purple" tables to save!

Barbed, Male Threaded Adapter Elbows

Nylon. Good chemical resistance. Temp range: -50 to 250°F (-46 to 121°C). Sterilize by ethylene oxide only.
PFA. Excellent chemical resistance. Temp range: 0 to 400°F (-17 to 204°C). Sterilize by ethylene oxide or autoclave.
Polypropylene (PP). Very good chemical resistance.
Black: Temp range: 9 to 180°F (-13 to 66°C). Sterilize by ethylene oxide or autoclave.
Clear: Temp range: 32 to 275°F (0 to 135°C). Sterilize by ethylene oxide or autoclave.

Natural: Temp range: 9 to 180°F (-13 to 66°C). Sterilize by ethylene oxide or gamma irradiation.
White: Temp range: 9 to 180°F (-13 to 66°C). Sterilize by autoclave only.
Stainless Steel (316 SS). Very good chemical resistance. Rated at 200 psi at 77°F (25°C). Temp range: -40 to 200°F (-40 to 93°C). Sterilize by ethylene oxide, autoclave, or gamma irradiation.

- Black PP
 - Chemfluor® PTFE
 - HDPE
 - Kynar®
 - Natural PP
 - Nylon
 - PFA
- ISO 9001:2000**
 CERTIFIED SUPPLIER

Tubing ID	Material	Key	Dimensions			Standard packs			Bulk packs		
			a	b	Orifice	Catalog number	Qty/ pk	Price/ pk	Catalog number	Qty/ pk	Price/ pk
NPT male threaded adapter elbows, NPT(M) x tubing ID—continued											
3/8" x 3/8"	HDPE	BJ	1 1/16"	1 1/32"	1/4"	K-30623-04	10		K-30627-04	100	
3/8" x 3/8"	Nylon	BK	1 1/16"	1 1/32"	1/4"	K-30623-05	10		K-30627-05	100	
3/8" x 3/8"	Natural PP	BM	1 1/16"	1 1/32"	1/4"	K-30610-60	10		K-30640-60	100	
3/8" x 3/8"	Kynar®	BN	1 1/16"	1 1/32"	1/4"	K-30704-39	10		—	—	—
3/8" x 1/2"	HDPE	BJ	1 1/16"	1 1/16"	1 1/32"	K-30623-06	10		K-30627-06	100	
3/8" x 1/2"	Nylon	BK	1 1/16"	1 1/16"	1 1/32"	K-30623-07	10		K-30627-07	100	
3/8" x 1/2"	Natural PP	BM	1 1/16"	1 1/16"	1 1/32"	K-30610-61	10		K-30640-61	100	
3/8" x 1/2"	Kynar®	BN	1 1/16"	1 1/16"	1 1/32"	K-30704-40	10		—	—	—
1/2" x 1/4"	HDPE	BJ	1 1/2"	1 19/32"	1/8"	K-30623-10	10		K-30627-10	100	
1/2" x 1/4"	Nylon	BK	1 1/2"	1 19/32"	1/8"	K-30623-11	10		K-30627-11	100	
1/2" x 1/4"	Natural PP	BM	1 1/2"	1 19/32"	1/8"	K-30610-62	10		K-30640-62	100	
1/2" x 1/4"	Kynar®	BN	1 1/2"	1 19/32"	1/8"	K-30704-41	10		—	—	—
1/2" x 3/8"	HDPE	BJ	1 21/32"	1 29/32"	1/4"	K-30623-12	10		K-30627-12	100	
1/2" x 3/8"	Nylon	BK	1 21/32"	1 29/32"	1/4"	K-30623-13	10		K-30627-13	100	
1/2" x 3/8"	Natural PP	BM	1 21/32"	1 29/32"	1/4"	K-30610-63	10		K-30640-63	100	
1/2" x 3/8"	Kynar®	BN	1 21/32"	1 29/32"	1/4"	K-30704-42	10		—	—	—
1/2" x 1/2"	HDPE	BJ	1 27/32"	1 29/32"	1 1/32"	K-30623-14	10		K-30627-14	100	
1/2" x 1/2"	Nylon	BK	1 27/32"	1 29/32"	1 1/32"	K-30623-15	10		K-30627-15	100	
1/2" x 1/2"	Natural PP	BM	1 27/32"	1 29/32"	1 1/32"	K-30610-64	10		K-30640-64	100	
1/2" x 1/2"	Kynar®	BN	1 27/32"	1 29/32"	1 1/32"	K-30704-43	10		—	—	—
1/2" x 5/8"	HDPE	BJ	1 5/32"	1 31/32"	1 15/16"	K-30623-08	10		K-30627-08	100	
1/2" x 5/8"	Nylon	BK	1 5/32"	1 31/32"	1 15/16"	K-30623-09	10		K-30627-09	100	
1/2" x 3/4"	HDPE	BJ	1 15/32"	1 5/8"	1 9/32"	K-30401-28	10		K-30401-02	100	
1/2" x 3/4"	Nylon	BK	1 15/32"	1 5/8"	1 9/32"	K-30401-01	10		K-30401-01	100	
1/2" x 3/4"	Natural PP	BM	2 3/16"	2 7/32"	9/16"	K-30610-65	10		K-30640-65	100	
1/2" x 3/4"	Kynar®	BN	2 1/8"	2 3/16"	9/16"	K-30704-44	10		—	—	—
1/2" x 1 1/2"	Black PP	BL	3 5/16"	1 5/16"	1/2"	K-31407-23	5		K-31417-23	50	
3/4" x 1/4"	Natural PP	BM	1 21/32"	1 5/8"	1/8"	K-30610-66	5		K-30640-66	50	
3/4" x 1/4"	Kynar®	BN	1 19/32"	1 19/32"	1/8"	K-30704-45	5		—	—	—
3/4" x 3/8"	Natural PP	BM	1 13/16"	1 25/32"	1/4"	K-30610-67	5		K-30640-67	50	
3/4" x 3/8"	Kynar®	BN	1 25/32"	1 3/4"	1/4"	K-30704-46	5		—	—	—
3/4" x 1/2"	HDPE	BJ	1 7/8"	2 1/8"	3/8"	K-06451-85	10		K-30401-20	100	
3/4" x 1/2"	Nylon	BK	1 7/8"	2 1/8"	3/8"	K-06466-55	10		K-30401-19	100	
3/4" x 1/2"	Natural PP	BM	2"	1 29/32"	1 1/32"	K-30610-68	5		K-30640-68	50	
3/4" x 1/2"	Kynar®	BN	1 15/16"	1 7/8"	1 1/32"	K-30704-47	5		—	—	—
3/4" x 5/8"	HDPE	BJ	1 7/8"	2 3/32"	1 5/32"	K-06451-90	10		K-30401-27	100	
3/4" x 5/8"	Nylon	BK	1 7/8"	2 3/32"	1 5/32"	K-30401-24	10		K-30401-26	100	
3/4" x 3/4"	HDPE	BJ	1 7/8"	2 3/8"	9/16"	K-30401-31	10		K-30401-23	100	
3/4" x 3/4"	Nylon	BK	1 7/8"	2 3/8"	9/16"	K-30401-21	10		K-30401-22	100	
3/4" x 3/4"	Natural PP	BM	2 5/16"	2 7/32"	9/16"	K-30610-69	5		K-30640-69	50	
3/4" x 3/4"	Kynar®	BN	2 3/32"	2 3/16"	9/16"	K-30704-48	5		—	—	—
3/4" x 1"	HDPE	BJ	2 1/16"	2 1/2"	1 9/16"	K-06477-17	10		K-30401-16	100	
3/4" x 1"	Nylon	BK	2 1/16"	2 1/2"	1 9/16"	K-30401-14	10		K-30401-15	100	
3/4" x 1"	Natural PP	BM	2 21/32"	2 1/2"	2 5/32"	K-30610-70	5		K-30640-70	550	
3/4" x 1"	Kynar®	BN	2 19/32"	2 1/16"	2 9/32"	K-30704-49	5		—	—	—
1" x 3/4"	HDPE	BJ	1 7/8"	2 13/32"	9/16"	K-06477-18	10		K-31701-27	100	
1" x 3/4"	Nylon	BK	1 7/8"	2 13/32"	9/16"	K-06478-18	10		K-31701-25	100	
1" x 1"	HDPE	BJ	2 1/16"	2 1/2"	1 9/16"	K-06477-19	10		K-30401-13	100	
1" x 1"	Nylon	BK	2 1/16"	2 1/2"	1 9/16"	K-06478-19	10		K-30401-12	100	
1" x 1"	Natural PP	BM	2 1/16"	2 1 1/16"	2 5/32"	K-30610-71	5		K-30640-71	50	
1" x 1"	Kynar®	BN	2 3/4"	2 5/8"	2 5/32"	K-30704-50	5		—	—	—
1 1/4" x 1"	Nylon	BK	2 1 1/16"	1 1/16"	5/16"	K-31408-21	5		K-31418-21	50	
1 1/4" x 1"	Black PP	BL	2 1 1/16"	1 1/16"	5/16"	K-31407-21	5		K-31417-21	50	
1 1/4" x 1 1/4"	Nylon	BK	3 1/16"	1 5/32"	1/2"	K-31408-22	5		K-31418-22	50	
1 1/4" x 1 1/4"	Black PP	BL	3 1/16"	1 5/32"	1 3/32"	K-31407-22	5		K-31417-22	50	
1 1/2" x 1 1/2"	Nylon	BK	3 9/16"	1 5/16"	7/16"	K-31408-23	5		K-31418-23	50	
2" x 2"	Nylon	BK	4 5/16"	1 11/16"	1 1/16"	K-31408-24	5		K-31418-24	50	
2" x 2"	Black PP	BL	4 5/16"	1 11/16"	1 1/16"	K-31407-24	5		K-31417-24	50	

NPT male threaded adapter elbows
(continued)



PTFE Thread Tape
 PTFE thread sealer tape prevents leaks and seepage at threads. PTFE tape withstands temperatures from -250 to 500°F (-157 to 260°C).
EG-08782-27 PTFE thread sealer tape.
 Roll measures 260"L x 1/2"W. Pack of 10 rolls
EG-08782-55 PTFE thread sealer string. Roll of 20 ft x 3/32"W

See next page for more...