



86366-00

Multifunction Digital Compass

Field-calibratable compass displays cardinal points and numeric headings

This water-resistant unit features a built-in compass, thermometer and clock. View temperature in °F or °C, time in 12- or 24-hour formats, date, and day of the week on the large LCD. Clock features both regular and snooze alarms. The bright blue backlight makes it easy to read at night or in dimly lit areas.

What's included: three AAA batteries, strap lanyard, and easy grip rubber case.

Specifications & Ordering Information

Power: three AAA batteries (included) **Dimensions:** 2 5/8" W x 5 1/2" H x 1" D

Catalog number	K-86366-00	
Parameter	Range	Accuracy
Direction	0 to 355° in 5° increments (N, E, NE, SE, S, SW, W, NW)	±20°
Temperature	32 to 140°F (0 to 60°C)	±2°F (±1°C)
Date	Month/Day	—
Time	0 to 24 hours (12- or 24-hr mode)	—
Price		



99841-06

Compact Multifunction Environmental Meters

Advanced compass technology in a durable, compact design

- Rugged, waterproof housing protects the meter in harsh environmental conditions

Meters feature a rubber-armored housing to withstand outdoor conditions. Measure temperature and feature a programmable temperature alarm, calendar, alarm clock with snooze, stop watch, count down timer, compass, and backlit LCD. Palm-size models also feature a map light. Select from a palm-size or wristwatch models to suit your needs. Also measure barometric pressure and altitude, feature a programmable altitude alarm, and display weather forecasts.

What's included: palm-size model includes two AAA batteries and a wrist strap. Wristwatch model includes one battery.



Specifications & Ordering Information

Power (included) **Dimensions:**
 Palm-size: two AA batteries Palm-size: 2"W x 4"H x 1" D
 Wristwatch: one CR2430 lithium battery Wristwatch: 2" diameter

Catalog number	K-99841-04	K-99841-06
Parameter	Palm-size	Wristwatch
Barometric pressure	260 to 1100 mbar, 7.65 to 32.45" Hg	260 to 1100 mbar, 7.65 to 32.45" Hg
Temperature	14 to 140°F (-10 to 60°C)	14 to 140°F (-10 to 60°C)
Altitude	-2,300 to 29,320 ft (-700 to 8940 m)	-2,300 to 29,320 ft (-700 to 8940 m)
Compass	0 to 359°	0 to 359°
Price		

99841-04

Environmental Meter

Complete environmental monitoring in the palm of your hand

This meter measures barometric pressure, temperature, and altitude. Scroll through parameter selection to display barometric pressure, temperature, altitude, compass function, time, or sunrise/sunset time. Backlit LCD constantly displays 12- to 24-hour weather forecast, moon phase, and sun and moon position. Bar graph displays 16-hour barometric pressure history. Audible alarm actuates with severe weather indication.

What's included: two lithium batteries.

Specifications & Ordering Information

Power: two CR2032 lithium batteries (included) **Dimensions:** 2 3/4" W x 4 1/2" H x 1" D

Catalog number	K-99756-18	
Parameter	Range	Accuracy
Barometric pressure	298 to 1100 mbar, 8.8 to 32.5" Hg	±1 mbar, ±0.025" Hg
Temperature	-4 to 158°F (-20 to 70°C)	±2°F (±1°C)
Altitude	-2296 to 29,527 ft (-700 to 9000 m)	—
Price		

99756-18

K-97152-60 Replacement battery; 3 V, type CR2032