

Continuous Ozone Monitors

Fixed or portable systems alert workers to hazardous ozone levels

- Easy-to-read, multicolor graphical display
- HMOS sensor for superior sensitivity

LED bar graph changes color as ozone levels increase: green indicates a safe level, yellow is caution level, and red is the danger level. Both models feature a heated metal oxide semiconductor (HMOS) sensor for excellent sensitivity and quick response time. Order optional calibrator to verify that your ozone monitors are conforming to their original calibration.

Fixed Ozone Monitor with Alarm has an audio alarm that is triggered at 0.1 ppm (danger level). Features include a connection for external equipment control. **Portable Ozone Monitor** can be permanently installed for on-site use or carried with you to detect leaks throughout your plant.

Specifications & Ordering Information



Display: LED color bar graph **Power:** Model 86316-10: AC adapter (included)
Output: 0 to 3 VDC Model 86316-20: rechargeable eight hour NiMH battery
Dimensions: 2¼"W x 3¼"H x 1¾"D and an AC adapter/recharger (included)

Catalog number	Description	Range	Price
KH-86316-10	Fixed ozone monitor with alarm	0.02 to 0.14 ppm (0.2 to 0.30 or more ppm with an external data readout)	
KH-86316-20	Portable ozone monitor	0.02 to 0.14 ppm	

[KH-86316-61](#) Ozone calibrator (0.1 ppm)



86316-10



Display 86316-20

Pocket Ozone Detector

Accurate, easy-to-read digital display

- Versatile meter can be used for fixed or portable monitoring
- Ideal for leak checks in generators, valves and piping

The heated metal oxide semiconductor has a range of 0.02 to 10 ppm; digital readout is in 0.01 ppm increments. Use as a permanent monitor indoors when the concentration average is below 0.1 ppm; use outdoors or at concentrations up to 10 ppm for short periods of time. Includes rechargeable batteries, charger, and carrying case.

Order optional calibrator to verify that your ozone monitor is conforming to the original calibration. Calibrator recalibrates detector at 0.1 ppm. It measures 2¼"W x 3¾"H x 1"D and includes a 9 V battery.

Specifications & Ordering Information



Display: LCD **Power:** rechargeable batteries with a charger (included) **Dimensions:** 2"W x 4"H x 1"D

Catalog number	Description	Range	Price
KH-86316-30	Ozone detector	0.02 to 10 ppm	

[KH-86316-61](#) Ozone calibrator (0.1 ppm)

[KH-09376-04](#) Replacement battery, 9 V. Pack of four



86316-30

Confined-Space Ventilation System

Portable axial blower with 15 feet of duct is self-contained—set it up in seconds!

This all-in-one ventilation system features a ⅓-hp, 8" axial blower that can move 1275 cfm of free air. Ductwork collapses into a built-in storage canister.

What's included: axial blower, canister, and 15-ft duct.



86352-00

Specifications & Ordering Information

Cat. no.	Description	Power	Price
KH-86352-00	Confined-space ventilation system	115 VAC, 3 A	