

OAKTON® Waterproof pHTestrs® 10, 20, and 30

Improved design with large, easy-to-read display

- A complete meter with key features at an economical price
- Replaceable, double-junction electrode sensors save time and money
- IP67-rated housing sits flat on the table and floats in water

Waterproof pHTestrs are great for outdoor applications such as taking pH measurements in lakes and streams. Designed to float in water, you can even attach a line to the housing for easy retrieval. Valox® sensor housing resists most chemicals.

All waterproof pHTestrs have replaceable sensors for easy maintenance. Double-junction electrode sensors handle wastewater and solutions containing sulfides, heavy metals, and TRIS. Electrode sensors offer a clog-resistant Kynar® junction and a recessed, glass pH bulb to protect against breakage.

The keypad clicks to confirm operation, and allows access to a variety of functions. Calibrate up to three pH points with the auto-buffer recognition at both USA and NIST standard buffers. Additional features include a hold function, automatic temperature compensation, auto-off function, self-diagnostic error messages, and a three-segment battery-life indicator.

pHTestr 10 offers the most economical option.

pHTestr 20 features ±0.01 pH accuracy—suitable for most ASTM and EPA test procedures.

pHTestr 30 includes all of the features of the pHTestr 20 along with dual pH and 0.1-resolution temperature display. Temperature display units in selectable °F or °C.



35634-10
pHTestr 10

35634-20
pHTestr 20

35634-30
pHTestr 30

Specifications & Ordering Information



Catalog number	KH-35634-10	KH-35634-20	KH-35634-30
Description	pHTestr 10	pHTestr 20	pHTestr 30 with temperature readout
Range	-1.0 to 15.0 pH		-1.00 to 15.00 pH
Resolution	0.1 pH		0.01 pH
Accuracy	±0.1 pH		±0.01 pH
Temperature compensation	Automatic, 32 to 122°F (0 to 50°C)		
Calibration	Up to three pH points		
Buffer recognition	4.0, 7.0, 10.0 USA 4.0, 6.9, 9.2 NIST		4.01, 7.00, 10.01 USA 4.01, 6.86, 9.18 NIST
Display	Four-digit LCD	Four-digit LCD	pH: 4-digit LCD; Temperature: 4-digit LCD
Power	Four 1.5 V button cell batteries (included)		
Battery life	More than 500 hours		
Dimensions	6½" L x 1½" dia		
Price			

KH-35624-38 Replacement pH sensor

KH-35624-45 Waterproof soft carrying case, built-in belt loop for easy transport. Holds a Testr and buffer pouches

KH-09377-16 Replacement batteries, 1.5 V. Pack of 6



Replaceable electrode—save money!



All Oakton® waterproof pHTestrs float!

OAKTON® Waterproof pHTestr® Calibration Kits

Store and organize all the components you need for fast, reliable calibration and measurement. The hard carrying case contains all the materials you need to calibrate in the field including premixed, premeasured buffers.

What's included: Waterproof pH tester (described above) except model 35624-70; two single-use pouches of pH 4.01, pH 7.00, pH 10.00 each, and rinse solution; one sample jar; and sturdy carrying case.

Ordering Information

Catalog number	Meter included	Price
KH-35624-70	None	
KH-35634-70	Waterproof pHTestr 10	
KH-35634-80	Waterproof pHTestr 20	
KH-35634-90	Waterproof pHTestr 30	



35634-90