

Waring Pro® Light-Duty Blenders

Economical blenders for light blending of ice and laboratory samples

- Polycarbonate, stainless steel, and glass containers accommodate use in food processing or industrial applications
- Powerful motor blends and homogenizes laboratory specimens

Choose from electronic membrane keypad or simple, two-speed toggle switch operation. Blenders with membrane keypad offer easy cleaning after common laboratory spills, and feature high, low, off, and pulse controls. Nonslip feet prevent blender from moving during operation. Blenders with toggle switch operation simplify repetitive blending and homogenization of routine laboratory specimens. Durable motor housing and removable blade assembly are easy to clean after use.

Containers offer easy-to-read English and metric graduations. Polycarbonate container offers internal visibility and strength. Stainless steel (SS) container is suitable for use in food testing labs.

What's included: container and blade assembly, and U.S. standard plug.



Blender 04242-92 with membrane keypad and polycarbonate container

New



Blender 04242-95 with two-speed toggle switch and glass container

Catalog number	Color	Container material	Capacity	Dimensions	Power		Shpg wt lb (kg)	Price
					VAC	Hz		
Light-duty blenders with electronic membrane keypad								
R-04242-92	Black	Polycarbonate	1.3 L	8"W x 13½"H x 9½"D	120	50/60	8 (3.6)	
R-04242-93	Black	SS	1 L					
Light-duty blenders with two-speed toggle switch								
R-04242-95	Chrome	Glass	1.2 L	8" W x 16½"H x 7"D	120	50/60	9 (4.1)	
R-04242-96	Black							

Waring Pro® Ice Crusher

Ideal benchtop machine for crushing ice

- Powerful motor crushes ice cubes into granular chips for use in benchtop ice buckets and pans
- Crushed ice easily fills flexible containers
- Compact design fits on lab bench or countertop

Ice crusher quickly crushes up to 30 pounds of ice per hour for immediate use at your benchtop. Crushed ice covers test tubes or centrifuge tubes more effectively than large ice cubes—ideal for lab applications that require specimens or enzymes to remain cold during testing. Brushed stainless steel housing is easy to clean and resists damage from harsh lab environments.

What's included: removable ice chute attachment and 12-cup ice container.

Catalog number	Color	Container material	Capacity	Dimensions	Power		Shpg wt lb (kg)	Price
					VAC	Hz		
R-04242-91	Silver	Polycarbonate	2.8 L	6"W x 15"H x 10"D	120	50/60	10 (4.5)	

New



Ice crusher 04242-91

Color-Coded Ice Buckets

Fill these ice buckets with crushed ice to keep your temperature-sensitive samples cool during testing. Lid included. Order additional ice buckets, ice pans, and floating tube racks separately on page 950.

GO to page(s) 947-951

For ice makers and additional ice storage products.

Catalog number	Color	Capacity	Dimensions	Price/ea
ED-06274-60	Black	3.8 liter	7" base OD x 10½" rim OD x 7" H	
ED-06274-62	Blue			
ED-06274-64	Red			
ED-06274-66	Green			
ED-06274-68	Yellow			

