

**buy more,  
save more**

5-9 pk/cs  
save 10%      10+ pk/cs  
save 15%

Mix and match packs or cases of items from "red" tables to save!

Mix and match packs of any items from the "red" tables to save!



17820-04

## COORST<sup>TEK</sup> Mortars and Pestles, Porcelain

Mortars and pestles are glazed all over except for grinding surfaces and the outside bottom of the mortar. Features lip, pour spout, and an oversized pestle for comfortable grinding. Mortar and pestle are sold as separate pieces. **Autoclavable.**

Piece	Cap. (mL)	Top OD (mm)	Height (mm)	Length (mm)	Catalog number	Qty/ pk	Price/ pk	Catalog number	Qty/ cs	Price/ cs
Mortar	65	80	53	—	R-17820-02	1	—	R-17820-22	18	—
Pestle	—	—	—	130	R-17821-02	1	—	R-17821-22	18	—
Mortar	145	90	70	—	R-17820-04	1	—	R-17820-24	12	—
Pestle	—	—	—	157	R-17821-04	1	—	R-17821-24	12	—
Mortar	275	115	70	—	R-17820-06	1	—	R-17820-26	8	—
Pestle	—	—	—	180	R-17821-06	1	—	R-17821-26	8	—
Mortar	400	130	80	—	R-17820-08	1	—	R-17820-28	8	—
Pestle	—	—	—	194	R-17821-08	1	—	R-17821-28	8	—
Mortar	750	163	110	—	R-17820-10	1	—	R-17820-30	4	—
Pestle	—	—	—	222	R-17821-10	1	—	R-17821-30	4	—
Mortar	1900	210	130	—	R-17820-12	1	—	R-17820-32	2	—
Pestle	—	—	—	262	R-17821-12	1	—	R-17821-32	2	—
Mortar	4000	283	150	—	—	—	—	R-17820-34	1	—
Pestle	—	—	—	280	—	—	—	R-17821-34	1	—



17822-28

## COORST<sup>TEK</sup> Mortars and Pestles, Alumina

Ideal for precise elemental analysis where minimal sample contamination is required. Mortars and pestles are glazed all over except for grinding surfaces and the outside bottom of the mortar. Feature an octagonal shape. Mortar and pestle are sold as separate pieces. **Autoclavable.**

Piece	Cap. (mL)	Top OD (mm)	Height (mm)	Length (mm)	Catalog number	Qty/ pk	Price/ pk	Catalog number	Qty/ cs	Price/ cs
Mortar	7	50	26	—	R-17822-02	1	—	R-17822-22	3	—
Pestle	—	—	—	57	R-17823-02	1	—	R-17823-22	3	—
Mortar	80	100	47	—	—	—	—	R-17822-28	1	—
Pestle	—	—	—	100	—	—	—	R-17823-28	1	—
Mortar	120	120	57	—	—	—	—	R-17822-30	1	—
Pestle	—	—	—	117	—	—	—	R-17823-30	1	—



04010-10

## Agate Mortar and Pestle Sets, Silicic Acid

Minimize sample contamination using these 99.91% silicic acid (SiO<sub>2</sub>) mortars and pestles. Ideal for samples of undetermined chemical composition. Feature an octagonal shape. Mortar and pestle are sold as a set. Replacement pestles are available—call our Application Specialists for details.

Mortars			Pestles		Catalog number	Qty/ st	Price/ st
Capacity (mL)	Top outside dia (mm)	Height (mm)	Length (mm)				
10	50	25	50		R-04010-00	1	—
15	65	25	65		R-04010-10		
25	75	30	75		R-04010-20		
30	80	35	80		R-04010-30		
50	100	40	100		R-04010-40	1	—
100	125	50	125		R-04010-50		
200	150	65	150		R-04010-60		



34500-55

## Mortar and Pestle Sets, Glass

Glass mortars offer a clear view of materials. Mortars are manufactured with a heavy molded base and lip for pouring. Mortars and pestles are sold as a set.

Mortars			Pestles		Catalog number	Qty/ st	Price/ st	Catalog number	Qty/ st	Price/ st
Capacity (mL)	Top outside dia (mm)	Height (mm)	Length (mm)							
50	60	45	80		R-34500-51	1	—	R-34501-51	6	—
100	80	60	100		R-34500-53	1	—	R-34501-53	6	—
250	100	75	120		R-34500-55	1	—	R-34501-57	6	—

### Ceramic Marking Ink

Use to permanently mark laboratory porcelain and ceramicware; apply with pen or brush. Markings become permanent when heated.

Catalog number	Description	Qty	Price
ED-17829-00	Ceramic marking ink	15 mL (0.5 oz)	—

