

buy more,  
save more

6-29 packs save 10%    30-119 packs save 15%    120+ packs save 20%

Mix and match packs of any items from the "blue" tables to save!

Wide-mouth style carboy



06056-22



Leakproof



Carboy with spigot  
06065-32

Larger carboys feature wide shoulder handles.



Carboy with tubulation  
06080-52 (tubing not included)

## NALGENE® Round Carboys, LDPE

Durable, leakproof LDPE carboys are ideal for holding corrosive materials. All 10-liter and larger carboys are graduated in 1-gallon and 5-liter increments and feature wide shoulder grips that make them easy to grasp. The 4-liter model 06065-10 has a shoulder tab-grip with an 11-mm hole. Polypropylene (PP) cap ensures leakproof seal.

Carboys with PP spigots accept 5/8" ID tubing and come with adapters for 1/4" and 1/2" ID tubing. Carboys with tubulation feature a hose barb, molded in at bottom of carboy for strength and leak resistance, which allows near-complete drainage. Tubing is not included—order on pages 2182-2233.

Catalog number	Liters (gallons)	Cap size	Qty/pk	Price/1 pk	Save 10% 6-29 pks	Save 15% 30-119 pks	Save 20% 120+ pks
<b>Carboys with shoulder handles</b>							
R-06031-32	10 (2½)	83B	1				
R-06031-42	15 (4)	83B					
R-06031-52	20 (5)	83B					
R-06031-62	25 (6½)	83B					
R-06031-72	50 (13)	83B					
<b>Wide-mouth carboys with shoulder handles</b>							
R-06056-22	10 (2½)	100 mm	1				
R-06056-32	15 (4)	100 mm					
R-06056-52	20 (5)	100 mm					
<b>Carboy with spigot and shoulder handles</b>							
R-06065-10	4 (1)	38-430	1				
R-06065-22	10 (2½)	83B					
R-06065-32	20 (5)	83B					
R-06065-52	25 (6½)	83B					
R-06065-62	50 (13)	83B					
<b>Carboys with 1/4" OD tubulation</b>							
R-06080-10	1 (¼)	38-430	1				
R-06080-20	2 (½)	38-430					
R-06080-30	4 (1)	38-430					
<b>Carboys with 1/2" OD tubulation and shoulder handles</b>							
R-06080-42	10 (2½)	83B	1				
R-06080-52	20 (5¼)	83B					
<b>Carboy with 5/8" OD tubulation and shoulder handles</b>							
R-06080-72	50 (13¼)	83B	1				

- R-06258-30 Replacement cap; PP, 83B. Pack of 2 ..... /pk
- R-63000-16 Replacement cap; PP, 100 mm. Pack of 12..... /pk
- R-63000-18 Replacement cap; PP, 38-430. Pack of 12..... /pk
- R-06070-22 Replacement spigot, PP.....

## NALGENE® Carboys, PC

Polycarbonate carboys are graduated in 1-gallon and 5-liter increments. Polypropylene (PP) cap with TPE gasket ensures leakproof seal. Carboys with PP spigots accept 5/8" ID tubing and come with adapters for 1/4" and 1/2" ID tubing. **Autoclavable.**

Catalog number	Liters (gallons)	Cap size	Qty/pk	Price/1 pk	Save 10% 6-29 pks	Save 15% 30-119 pks	Save 20% 120+ pks
<b>Carboys</b>							
R-06063-60	10 (2½)	83B	1				
R-06063-62	20 (5)	83B					
<b>Carboys with spigot</b>							
R-06063-80	10 (2½)	83B	1				
R-06063-82	20 (5)	83B					

- R-06070-22 Replacement spigot, PP.....
- R-06258-30 Replacement caps; PP, 83B. Pack of 2..... /pk



06063-60

06063-82

**GO to page(s) 251**  
To order filling/venting caps.



**GO to ColeParmer.com**  
ColeParmer.com/Carboys

For our complete product line of carboys.