

Gloves

Disposable Nitrile

Personal Protective Equipment

KIMTECH SCIENCE® Blue Nitrile Exam Gloves

Superior fit and comfort

These powder-free nitrile gloves are soft, comfortable, and minimize hand irritation due to glove powder. Latex-free gloves reduce the potential for allergic reactions to natural rubber latex. Textured fingertips enhance grip. Ambidextrous.

Compliance: ASTM D 6319, ISO 9002.



86313-62

Catalog number	Size	Length	Thickness	Qty/bx	Price per box	
					1 bx	10 bx
YS-86313-60	Small	9½"	6 mil	100		
YS-86313-61	Medium			100		
YS-86313-62	Large			100		
YS-86313-63	X-large			90		

KIMTECH SCIENCE® Nitrile Exam Gloves

Purple color easily distinguishes these gloves from latex

These 100% nitrile gloves are soft, latex-free, powder-free, and nonsticky. Low chemical content reduces risk of allergic reactions. Textured fingertips enhance wet or dry grip. Beaded cuff. Available in 9½" lengths or 12" extended cuff. Ambidextrous.

Compliance: ASTM D 6319, ISO 9002.



86313-21

Catalog number	Size	Length	Thickness	Qty/bx	Price per box		
					1 bx	10 bx	
YS-86313-20	Small	9½"	5 mil	100			
YS-86313-21	Medium			100			
YS-86313-22	Large			100			
YS-86313-23	X-large			90			
YS-86313-30	Small	12"	5 mil	50			
YS-86313-31	Medium						
YS-86313-32	Large						
YS-86313-33	X-large						

AURELIA Protégé™ Nitrile Gloves

Improved protection, amazing comfort

- 100% latex-free, powder-free

These blue, stretchy nitrile gloves offer the comfort of latex without the associated allergic reaction. Plus, the nitrile material provides greater chemical compatibility compared to other materials. Gloves offer superior sensitivity and have textured fingertips for precise gripping. Ambidextrous.



86246-41


Catalog number	Size	Length	Thickness	Qty/bx	Price per box		
					1 bx	10 bx	
YS-86246-40	Small	9½"	4 mil	100			
YS-86246-41	Medium						
YS-86246-42	Large						
YS-86246-43	X-large						

AURELIA Robust™ Nitrile Gloves

Micro-textured finish offers a sure grip in wet environments

- Nonlatex, protein-free, powder-free

Made from a special nitrile compound, these blue gloves provide comfortable fit, durable wear, and tactile sensitivity. Micro-textured finish for superior grip in wet or dry conditions. Beaded cuffs for easy donning and added protection. For single use only. Ambidextrous.



86246-21



Catalog number	Size	Length	Thickness	Qty/bx	Price per box		
					1 bx	10 bx	
YS-86246-20	Small	9½"	6 mil	100			
YS-86246-21	Medium						
YS-86246-22	Large						
YS-86246-23	X-large						

KIMTECH SCIENCE® HypoClean Critical™ Nitrile Gloves

Extend cuffs are beaded for easier donning

HypoClean Critical™ cleanroom gloves have excellent ESD characteristics. These 100% latex-free nitrile gloves have been rinsed several times in deionized water—greatly reducing particulates, ion extractables, and NVR levels. Tapered, long beaded cuffs grip your garment sleeves securely; double gloving is effortless. Bag-in-bag packaged in cleanroom compatible materials. Ambidextrous.

Compliance: ISO Class 5; ISO 9002

ISO CLASS 5



86313-01

Catalog number	Size	Length	Thickness	Qty/bg	Price per bag		
					1 bg	10 bg	
YS-86313-00	Small	12"	4 mil	100			
YS-86313-01	Medium						
YS-86313-02	Large						
YS-86313-03	X-Large						

GO to page(s) iv-8

For a wide range of apparel including lab coats, aprons, and coveralls.

