

**Cole-Parmer**  
Peroxide Silicone Tubing



**Applications:** Pharmaceutical, biotechnology, food and beverage, aerospace, and general lab applications.  
**Characteristics:** Peroxide-cured, excellent heat resistance, low compression set, odorless, nontoxic, translucent.  
**Resin certification:** Resin is FDA-compliant (21 CFR 177.2600) and meets USP Class VI requirements. Tubing is manufactured according to GMP.  
**Temperature range:** -60 to 460°F (-51 to 238°C)  
**Sterilize:** Autoclave or gamma irradiation.

Catalog number	Dimensions: in. (mm)			Max psi at 70°F	Price/25-ft pk
	ID	OD	Wall		
KH-06411-59	1/50 (0.5)	1/12 (2.1)	1/32 (0.8)	30	
KH-06411-60	1/32 (0.8)	3/32 (2.4)	1/32 (0.8)	31	
KH-06411-62	1/16 (1.6)	1/8 (3.2)	1/32 (0.8)	15	
KH-06411-63	3/32 (2.4)	5/32 (4.0)	1/32 (0.8)	14	
KH-06411-64	1/8 (3.2)	3/16 (4.8)	1/32 (0.8)	10	
KH-06411-67	1/8 (3.2)	1/4 (6.4)	1/16 (1.6)	21	
KH-06411-68	1/8 (3.2)	3/8 (9.6)	1/8 (3.2)	25	
KH-06411-65	5/32 (4.0)	7/32 (4.0)	1/32 (0.8)	10	
KH-06411-66	3/16 (4.8)	1/4 (6.4)	1/32 (0.8)	9	
KH-06411-03	3/16 (4.8)	5/16 (8.0)	1/16 (1.6)	13	
KH-06411-69	3/16 (4.8)	7/16 (11.2)	1/8 (3.2)	22	
KH-06411-70	1/4 (6.4)	5/16 (8.0)	1/32 (0.8)	8	
KH-06411-71	1/4 (6.4)	3/8 (9.6)	1/16 (1.6)	12	
KH-06411-72	1/4 (6.4)	7/16 (11.2)	3/32 (2.4)	17	
KH-06411-74	1/4 (6.4)	1/2 (12.8)	1/8 (3.2)	17	
KH-06411-75	5/16 (8.0)	7/16 (11.2)	1/16 (1.6)	10	
KH-06411-76	5/16 (8.0)	1/2 (12.8)	3/32 (2.4)	16	
KH-06411-77	5/16 (8.0)	9/16 (14.4)	1/8 (3.2)	20	
KH-06411-12	3/8 (9.6)	1/2 (12.8)	1/16 (1.6)	10	
KH-06411-78	3/8 (9.6)	9/16 (14.4)	3/32 (2.4)	12	
KH-06411-79	3/8 (9.6)	5/8 (16.0)	1/8 (3.2)	14	
KH-06411-80	1/2 (12.8)	5/8 (16.0)	1/16 (1.6)	8	
KH-06411-19	1/2 (12.8)	11/16 (17.6)	3/32 (2.4)	10	
KH-06411-55	1/2 (12.8)	3/4 (19.2)	1/8 (3.2)	12	
KH-06411-82	5/8 (16.0)	13/16 (20.8)	3/32 (2.4)	10	
KH-06411-58	5/8 (16.0)	7/8 (22.4)	1/8 (3.2)	12	
KH-06411-83	3/4 (19.2)	1 (25.4)	1/8 (3.2)	9	

**Cole-Parmer**  
Platinum Silicone Tubing



**Applications:** Pharmaceutical, biotechnology, aerospace, food and beverage, and general lab applications.  
**Characteristics:** Platinum-cured, excellent heat resistance, low compression set, odorless, nontoxic, translucent.  
**Resin certification:** Resin is FDA-compliant (21 CFR 177.2600) and meets USP Class VI; exceeds 3A Sanitary Standards. Tubing is manufactured according to GMP.  
**Temperature range:** -58 to 446°F (-50 to 230°C)  
**Sterilize:** Autoclave or gamma irradiation.

Catalog number	Dimensions: in. (mm)			Max psi at 70°F	Price/25-ft pk
	ID	OD	Wall		
KH-95802-00	1/50 (0.5)	1/12 (2.1)	1/32 (0.8)	30	
KH-95802-01	1/32 (0.8)	3/32 (2.4)	1/32 (0.8)	31	
KH-95802-02	1/16 (1.6)	1/8 (3.2)	1/32 (0.8)	15	
KH-95802-03	3/32 (2.4)	5/32 (4.0)	1/32 (0.8)	14	
KH-95802-04	1/8 (3.2)	3/16 (4.8)	1/32 (0.8)	10	
KH-95802-05	1/8 (3.2)	1/4 (6.4)	1/16 (1.6)	21	
KH-95802-06	1/8 (3.2)	3/8 (9.6)	1/8 (3.2)	25	
KH-95802-07	5/32 (4.0)	7/32 (4.0)	1/32 (0.8)	10	
KH-95802-08	3/16 (4.8)	1/4 (6.4)	1/32 (0.8)	9	
KH-95802-09	3/16 (4.8)	5/16 (8.0)	1/16 (1.6)	13	
KH-95802-10	3/16 (4.8)	7/16 (11.2)	1/8 (3.2)	22	
KH-95802-11	1/4 (6.4)	5/16 (8.0)	1/32 (0.8)	8	
KH-95802-12	1/4 (6.4)	3/8 (9.6)	1/16 (1.6)	12	
KH-95802-13	1/4 (6.4)	7/16 (11.2)	3/32 (2.4)	17	
KH-95802-14	1/4 (6.4)	1/2 (12.8)	1/8 (3.2)	17	
KH-95802-15	5/16 (8.0)	7/16 (11.2)	1/16 (1.6)	10	
KH-95802-16	5/16 (8.0)	1/2 (12.8)	3/32 (2.4)	16	
KH-95802-17	5/16 (8.0)	9/16 (14.4)	1/8 (3.2)	20	
KH-95802-18	3/8 (9.6)	1/2 (12.8)	1/16 (1.6)	10	
KH-95802-19	3/8 (9.6)	9/16 (14.4)	3/32 (2.4)	12	
KH-95802-20	3/8 (9.6)	5/8 (16.0)	1/8 (3.2)	14	
KH-95802-21	1/2 (12.8)	5/8 (16.0)	1/16 (1.6)	8	
KH-95802-22	1/2 (12.8)	11/16 (17.6)	3/32 (2.4)	10	
KH-95802-23	1/2 (12.8)	3/4 (19.2)	1/8 (3.2)	12	
KH-95802-24	5/8 (16.0)	13/16 (20.8)	3/32 (2.4)	10	
KH-95802-25	5/8 (16.0)	7/8 (22.4)	1/8 (3.2)	12	
KH-95802-26	3/4 (19.2)	1 (25.4)	1/8 (3.2)	9	

**Tygon® BioPharm Silicone Tubing**



**Formulation:** Tygon® 3350 silicone, platinum cured.  
**Applications:** Pharmaceutical, cosmetic, industrial, and auto-analysis applications.  
**Characteristics:** Ultra-smooth inner surface reduces particle entrapment and minimizes bacterial growth. Good for mild to medium concentration bases, salts, and alcohols; is odorless, tasteless, and nontoxic. Transparent.  
**Resin certification:** Resin is FDA-compliant (21 CFR 177.2600) and meets USP Class VI requirements, and NSF criteria. Tubing is manufactured according to GMP.  
**Temperature range:** -112 to 392°F (-80 to 200°C)  
**Sterilize:** Ethylene oxide, gamma irradiation, or autoclave for 30 min, 15 psi.

Catalog number	Dimensions: in. (mm)			Max psi at 73°F	Price/50-ft pk
	ID	OD	Wall		
KH-95702-00	1/32 (0.8)	3/32 (2.4)	1/32 (0.8)	16	
KH-95702-01	1/16 (1.6)	1/8 (3.2)	1/32 (0.8)	10	
KH-95702-02	1/16 (1.6)	3/16 (4.8)	1/16 (1.6)	15	
KH-95702-03	3/32 (2.4)	5/32 (4.0)	1/32 (0.8)	7	
KH-95702-04	3/32 (2.4)	7/32 (5.6)	1/16 (1.6)	12	
KH-95702-05	1/8 (3.2)	3/16 (4.8)	1/32 (0.8)	7	
KH-95702-06	1/8 (3.2)	1/4 (6.4)	1/16 (1.6)	9	
KH-95702-08	3/16 (4.8)	1/4 (6.4)	1/32 (0.8)	5	
KH-95702-09	3/16 (4.8)	5/16 (8.0)	1/16 (1.6)	7	
KH-95702-10	3/16 (4.8)	3/8 (9.6)	3/32 (2.4)	9	
KH-95702-13	1/4 (6.4)	3/8 (9.6)	1/16 (1.6)	5	
KH-95702-14	1/4 (6.4)	7/16 (11.2)	3/32 (2.4)	7	
KH-95702-16	5/16 (8.0)	7/16 (11.2)	1/16 (1.6)	5	
KH-95702-17	5/16 (8.0)	1/2 (12.8)	3/32 (2.4)	6	
KH-95702-18	3/8 (9.6)	1/2 (12.8)	1/16 (1.6)	4	
KH-95702-19	3/8 (9.6)	9/16 (14.4)	3/32 (2.4)	5	
KH-95702-20	3/8 (9.6)	5/8 (16.0)	1/8 (3.2)	7	
KH-95702-25	1/2 (12.8)	3/4 (19.2)	1/8 (3.2)	5	
KH-95702-27	5/8 (16.0)	7/8 (22.4)	1/8 (3.2)	4	
KH-95702-28	3/4 (19.2)	1 (25.4)	1/8 (3.2)	4	