

Hubtron Basic™ Fluoroelastomer Tubing



Applications: General chemical transfer, electronic applications, ink and general printing applications.

Characteristics: Low leachables. Transparent.

Resin certification: None.

Temperature range: 14 to 248°F (-10 to 120°C)

Sterilization: Autoclave.

| Catalog number | Dimensions: in. (mm) | | | Price/25-ft pk |
|-----------------------------|----------------------|-------------|------------|----------------|
| | ID | OD | Wall | |
| KH-95225-00 | 1/16 (1.6) | 3/16 (4.8) | 1/16 (1.6) | |
| KH-95225-02 | 1/8 (3.2) | 1/4 (6.4) | 1/16 (1.6) | |
| KH-95225-04 | 3/16 (4.8) | 5/16 (8.0) | 1/16 (1.6) | |
| KH-95225-06 | 1/4 (6.4) | 3/8 (9.6) | 1/16 (1.6) | |
| KH-95225-08 | 5/16 (8.0) | 7/16 (11.2) | 1/16 (1.6) | |

Hubtron Advance™ Fluoroelastomer Tubing



Applications: Corrosive chemical transfer, electronic applications, ink and general printing applications, and automotive applications.

Characteristics: Very low gas permeability, highly chemical compatible. Inner fluoroplastic liner, outer fluoroelastomer cover—smooth inner lining. Excellent alcohol, ester, acid and alkali resistance. Transparent.

Resin certification: None.

Temperature range: 14 to 248°F (-10 to 120°C)

Sterilization: Autoclave.

| Catalog number | Dimensions: in. (mm) | | | Price/25-ft pk |
|-----------------------------|----------------------|-------------|------------|----------------|
| | ID | OD | Wall | |
| KH-95226-00 | 1/16 (1.6) | 3/16 (4.8) | 1/16 (1.6) | |
| KH-95226-02 | 1/8 (3.2) | 1/4 (6.4) | 1/16 (1.6) | |
| KH-95226-04 | 3/16 (4.8) | 5/16 (8.0) | 1/16 (1.6) | |
| KH-95226-06 | 1/4 (6.4) | 3/8 (9.6) | 1/16 (1.6) | |
| KH-95226-08 | 5/16 (8.0) | 7/16 (11.2) | 1/16 (1.6) | |

Hubtron Pascal™ Fluoroelastomer Tubing



Applications: Extremely demanding corrosive chemical transfer, electronic applications, ink and general printing applications, automotive applications, general mechanical applications.

Characteristics: Superior pressure ratings, extremely strong chemical resistance, extremely low permeability. Excellent resistance to solvents, acids, bases, alcohols and esters. Transparent.

Resin certification: None.

Temperature Range: 14 to 248°F (-10 to 120°C)

Sterilization: Autoclave.

| Catalog number | Dimensions: in. (mm) | | | Price/25-ft pk |
|-----------------------------|----------------------|-------------|------------|----------------|
| | ID | OD | Wall | |
| KH-95227-00 | 1/16 (1.6) | 3/16 (4.8) | 1/16 (1.6) | |
| KH-95227-02 | 1/8 (3.2) | 1/4 (6.4) | 1/16 (1.6) | |
| KH-95227-04 | 3/16 (4.8) | 5/16 (8.0) | 1/16 (1.6) | |
| KH-95227-06 | 1/4 (6.4) | 3/8 (9.6) | 1/16 (1.6) | |
| KH-95227-08 | 5/16 (8.0) | 7/16 (11.2) | 1/16 (1.6) | |

Static-Dissipative Polyurethane Tubing

New



Applications: Air lines, especially for electronic leads and component assembly.

Characteristics: Dissipates static electricity. No migratory chemical additives; no conductive fillers. Low gas permeability; no detectable particle emission. Opaque white.

Resin certification: None.

Temperature range: -40 to 165°F (-40 to 74°C)

Sterilize: Not recommended.

| Catalog number | Dimensions: in. (mm) | | | Max psi at 70° F | Price/100-ft pk |
|-----------------------------|----------------------|------------|------------|------------------|-----------------|
| | ID | OD | Wall | | |
| KH-65535-00 | 1/16 (1.6) | 1/8 (3.2) | 1/32 (0.8) | 90 | |
| KH-65535-02 | 3/64 (2.0) | 3/32 (6.4) | 1/26 (1.0) | 85 | |
| KH-65535-04 | 1/8 (3.2) | 1/4 (6.4) | 1/16 (1.6) | 85 | |
| KH-65535-06 | 1/4 (6.4) | 3/8 (9.5) | 1/16 (1.6) | 65 | |

EVA (Ethyl Vinyl Acetate) Microbore Tubing



Applications: Ideal for clinical and biological testing.


Characteristics: Cross-linked tubing is biologically stable, nontoxic, and noncontaminating. Flexible Micro-Line™ tubing has virtually 100% elastic memory—returns to its original shape with gentle heating. Tensile strength is 2700 psi; durometer hardness is Shore-A 90. Translucent.

Resin certification: Resin is FDA-compliant (21 CFR 177.1350), USP Class VI, and National Formulary Vol. 14 specifications.

Temperature range: -29 to 180°F (-34 to 82°C)

Sterilize: Autoclave, ethylene oxide, gamma irradiation, or dry heat.

See page 2167.



| Catalog number | Dimensions: in. (mm) | | | Fits needle gauge | Price/100-ft roll |
|-----------------------------|----------------------|--------------|--------------|-------------------|-------------------|
| | ID | OD | Wall | | |
| KH-06492-02 | 0.020 (0.51) | 0.060 (1.52) | 0.020 (0.51) | 25 | |
| KH-06492-03 | 0.030 (0.76) | 0.090 (2.29) | 0.030 (0.76) | 20 to 21 | |
| KH-06492-04 | 0.040 (1.02) | 0.070 (1.78) | 0.015 (0.38) | 18 to 19 | |
| KH-06492-05 | 0.050 (1.27) | 0.090 (2.29) | 0.020 (0.51) | 17 to 18 | |

GO to ColeParmer.com

Search online for all our new items—product lines are continually updated!

[Click Here](#)